

NOVATECH

ITB 200X50-Ø25 HL54

EAN 4031582397956
Order number 00861403



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Bore with keyway
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Axle hole diameter	25 mm
Hub length	54 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	960 kg
Load capacity at 6 km/h	800 kg
Load capacity Static	1600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	1.21 kg

NOVATECH

ITB 200X50- ϕ 25 HL54

EAN 4031582397956
Order number 00861403



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

