

# ELASTECH

UEP 200x46-Ø20

EAN 4031582328608



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Tread hardness	soft
Body material	Polyamide
Tread Material Mix	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	200 mm
Tread width	46 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Body width	46 mm
Hardness of tread (A)	63 Shore A

## PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●●●
Attrition	●●●○●
Corrosion Resistance	●●●○●

## CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Electric Conductive	No
Stainless	No
Load capacity Static	800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	1.24 kg

# ELASTECH

UEP 200x46-Ø20

EAN 4031582328608

Order number 00023479

Product Drawings



BETTER MOBILITY. BETTER LIFE.

