

# OMIKRON

9250STP300P66

EAN 4031582314052  
Order number 00830229



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Omikron
Housing type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	3120 kg
Load capacity at 6 km/h	2600 kg
Load capacity Static	6240 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	370 mm
Overall weight	42.031 kg

## WHEEL

Body material	Sheet steel, heavy
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	300 mm
Tread width	100 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Straight
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	90 mm
Swivel radius	240 mm
Swivel interference	480 mm

## FITTING

Fitting type	Rectangular plate
Plate length	250 mm
Plate width	200 mm
Plate hole length (Maximum)	210 mm
Plate hole width (Maximum)	160 mm
Plate hole diameter	17 mm

# OMIKRON

9250STP300P66

EAN 4031582314052  
Order number 00830229

## TECHNICAL DRAWINGS

