

DURATECH

UOR150X46-Ø20 HL58

EAN 4031582496680
Order number 10000776



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	5.91 in
Tread width	1.81 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1102.31 lb
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	1.26 lb

PRODUCT INFORMATION

DURATECH

UOR150X46-Ø20 HL58

EAN 4031582496680
Order number 10000776



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

