

ALPHA LIGHT

3438POO065P60-95X54 ZWART (16)

EAN 4031582214581



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha light
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	120 kg
Load capacity Static	240 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	83 mm
Overall weight	0.234 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	65 mm
Tread width	30 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad

FITTING

Fitting type	Rectangular plate
Plate length	95 mm
Plate width	54 mm
Plate hole length (Maximum)	71 mm
Plate hole width (Maximum)	24 mm
Plate hole diameter	9 mm

ALPHA LIGHT

3438POO065P60-95X54 ZWART (16)

EAN 4031582214581



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

