

STYLEA

5920UJI075B10-11X20/10D20 9011/7016

EAN 4031582310795



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Stylea
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	77 mm
Overall width	54 mm
Overall weight	0.18 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	30 mm
Swivel radius	62 mm
Swivel interference	124 mm
Dome diameter	20 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread Color	Anthracite grey (RAL7016)
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	75 mm
Tread width	8 mm
Axle Hole Diameter	0 mm
Hub Length	0 mm
Body width	8 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm
Stem length	20 mm

STYLEA

5920UJI075B10-11X20/10D20 9011/7016

EAN 4031582310795

Order number 00071011

Product Drawings



BETTER MOBILITY. BETTER LIFE.

