PRODUCT INFORMATION

ELASTECH

SFP 160x50-Ø20 HL60 plus

EAN 4031582322200



Image may differ from the original product

PERFORMANCE

Roll Performance	●●○○○
Movement Noise	●●●●●
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	540 kg
Load capacity at 6 km/h	450 kg
Electric Conductive	No
Stainless	No
Load capacity Static	900 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	1.12 kg

WHEEL

Tread hardness	soft
Body material	Sheet steel, heavy
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Wheel Color	Grey / non marking
Threadguards	With threadguard
Diameter	160 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Body width	50 mm
Hardness of tread (A)	68 Shore A

© Copyright 2026 TENTE International GmbH


ELASTECH

SFP 160x50-Ø20 HL60 plus

EAN 4031582322200

Order number 00830558

Product Drawings




© Copyright 2026 TENTE International GmbH

ELASTECH

SFP 160x50-Ø20 HL60 plus

EAN 4031582322200

Order number 00830958



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH