

NOVATECH

ETP095X40-Ø20 HL45

EAN 4031582330403



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3.74 in
Tread width	1.57 in
Axle hole diameter	0.79 in
Hub length	1.77 in
Hardness of tread (A)	92 Shore A
Bearing type	6204ZV

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 1.8 mph	881.85 lb
Load capacity Static	1763.7 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	3.49 lb

TECHNICAL DRAWINGS

