PRODUCT INFORMATION

STYLEA

5925UJI075P41-38X38 TFR

EAN 4031582385748



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel caster with wheel brake
Standard	EN12528 - Furniture Castors
Electric conductive	no
Stainless	no
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	3.43 in
Overall width	2.09 in
Overall weight	0.46 lb

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	2.44 in
Swivel interference	4.88 in
Dome diameter	0.79 in

WHEEL

Body material	Polyamide
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.31 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Square plate
Plate length	1.5 in
Plate width	1.5 in
Plate hole length (Maximum)	1.1 in
Plate hole width (Maximum)	1.1 in
Plate hole diameter	0.17 in

© Copyright 2026 TENTE International GmbH