

# NOVATECH

ETP 085X115-Ø30 HL115

EAN 4031582330380  
Order number 00839737



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	3.35 in
Tread width	4.53 in
Axle hole diameter	1.18 in
Hub length	4.53 in
Body width	4.53 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Bearing type	6006

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1873.93 lb
Load capacity at 3.7 mph	1499.14 lb
Load capacity Static	3747.85 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	3.36 lb

# NOVATECH

ETP 085X115-Ø30 HL115

EAN 4031582330380  
Order number 00839737



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

