

MAXTECH

DNP200X50-Ø20X50

EAN 4031582380996



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Load capacity at 1.8 mph	165.35 lb
Electric conductive	✓
Load capacity Static	330.69 lb
Overall weight	1.9 lb

WHEEL

Body material	Sheet Steel
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	1.97 in

MAXTECH

DNP200X50-Ø20X50

EAN 4031582380996



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

