

NOVATECH

ITP150X50-Ø20 HL54

EAN 4031582456776



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Aluminium |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Threadguards | Without threadguard |
| Diameter | 150 mm |
| Tread width | 50 mm |
| Axle hole diameter | 20 mm |
| Hub length | 54 mm |
| Hardness of tread (A) | 92 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Novatech |
| Housing type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 650 kg |
| Load capacity at 6 km/h | 520 kg |
| Load capacity Static | 1300 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 1.177 kg |

TECHNICAL DRAWINGS

