

# SOCKET

Kunststoff Huelse R40-22/11

EAN 4031582090192



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

Fitting type	Synthetic socket, square
Bolt diameter	22 mm

## PERFORMANCE

Corrosion Resistance ●●●○○

## CORE ATTRIBUTES

Product Name	Socket
Type	Accessory
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Overall Height	36 mm
Overall weight	0.01 kg

# SOCKET

Kunststoff Huelse R40-22/11

EAN 4031582090192

Order number 00009046  
Product Drawings



BETTER MOBILITY. BETTER LIFE.



Bezeichnung	A	B	C
R40-16x16	16	20	36
R40-17x17	17	19	36
R40-18x18	18	20	36
R40-21x21	21	23,5	36
R40-22x22	22	24,5	36
R40-23x23	23	25,5	36
R40-26x26	26	30	36