

PURETECH

JYX 150x32-Ø8,3 clip

EAN 4031582319972



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Zinc die-cast
Tread Material Mix	Solid rubber, black, electric-conductive
Bearing	Precision ball bearing, sealed
Wheel Color	Metallic
Threadguards	With threadguard
Diameter	150 mm
Tread width	32 mm
Axle Hole Diameter	8.3 mm
Hub Length	35.5 mm
Body width	32 mm
Hardness of tread (A)	75 Shore A

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	150 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	300 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	0.89 kg

PURETECH

JYX 150x32-Ø8,3 clip

EAN 4031582319972

Order number 00024890
Product Drawings



BETTER MOBILITY. BETTER LIFE.

