

# ALPHA STAINLESS

8477UFD100P30-11

EAN 4031582370188



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	330.69 lb
Stainless	✓
Load capacity Static	661.39 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall height	5.04 in
Overall weight	1.98 lb

## WHEEL

Body material	Polyamide
	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Diameter	3.94 in
Tread width	1.34 in
Hardness of tread (A)	64 Shore A

## HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.61 in
Swivel interference	9.53 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in

# ALPHA STAINLESS

8477UFD100P30-11

EAN 4031582370188



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

