

# EXPANDER

R07-Ø27/30 INOX

EAN 4031582425178



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	27 mm
Expander fitting (Maximum)	30 mm
Hint	Please indicate required tube innerdiameter when ordering.

## PERFORMANCE

Corrosion Resistance	● ● ● ○ ○
----------------------	-----------

## CORE ATTRIBUTES

Product Name	Expander
Type	Accessory
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall weight	0.14 kg