

PRODUCT INFORMATION

ELASTECH

UFR125x40-Ø20 Blue

EAN 4031582436686



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------------------|
| Tread hardness | soft |
| Body material | Polyamide |
| Tread Material Mix | Elastic tire, non-marking, vulcanized |
| Bearing | Roller bearing |
| Threadguards | Without threadguard |
| Diameter | 125 mm |
| Tread width | 40 mm |
| Axle Hole Diameter | 12 mm |
| Hub Length | 44,4 mm |
| Hardness of tread (A) | 64 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ○ ○ |
| Movement Noise | ● ● ● ● ● |
| Attrition | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product Name | Elastech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 250 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 500 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.42 kg |