

# AGILA TWIN

2970PJH075P30-10,3

EAN 4031582439489



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Agila twin                |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 100 kg                    |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 200 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 85 °C                     |
| Overall Height              | 99 mm                     |
| Overall weight              | 0.75 kg                   |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Twin wheel housing  |
| Swivel Bearing      | Two ball races      |
| Offset              | 31.4 mm             |
| Swivel radius       | 68.9 mm             |
| Swivel interference | 137.8 mm            |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread Material Mix    | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | With threadguard     |
| Diameter              | 75 mm                |
| Tread width           | 25 mm                |
| Hardness of tread (A) | 87 Shore A           |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 10.3 mm   |

# AGILA TWIN

2970PJH075P30-10,3

EAN 4031582439489



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

