

SUPRATECH

PJP125x32-Ø8,3 2.0

EAN 4031582070



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
CO2 emission (scope 3)	0.99
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.52 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.26 in
Axle hole diameter	0.31 in
Hub length	1.44 in
Hardness of tread (A)	85 Shore A

SUPRATECH

PJP125x32-Ø8,3 2.0

EAN 4031582070

Order number 10010291

Product Drawings



BETTER MOBILITY. BETTER LIFE.

