

# LEVINA

5370PIP100P50

EAN 4031582362701



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Levina                    |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 80 kg                     |
| Load capacity Static        | 160 kg                    |
| Temperature range (Minimum) | -10 °C                    |
| Temperature range (Maximum) | 40 °C                     |
| Overall height              | 137 mm                    |
| Overall weight              | 0.475 kg                  |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Solid rubber, non-marking |
| Bearing               | Precision ball bearing    |
| Threadguards          | With threadguard          |
| Diameter              | 100 mm                    |
| Tread width           | 32 mm                     |
| Hardness of tread (A) | 75 Shore A                |

## HOUSING

|                     |                |
|---------------------|----------------|
| Material fork       | Polyamide      |
| Fork shape          | Slim           |
| Swivel bearing      | Two ball races |
| Offset              | 36 mm          |
| Swivel radius       | 86 mm          |
| Swivel interference | 172 mm         |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 77 mm             |
| Plate width                 | 67 mm             |
| Plate hole length (Minimum) | 56 mm             |
| Plate hole length (Maximum) | 61.5 mm           |
| Plate hole width (Minimum)  | 46.5 mm           |
| Plate hole width (Maximum)  | 51.5 mm           |
| Plate hole diameter         | 8.5 mm            |



Universal  
Design  
Award



Deutscher  
Designer  
Club

# LEVINA

5370PIP100P50

EAN 4031582362701



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

