

# LEVINA LIGHT

5225PJP075L51-10

EAN 4031582477061



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Levina light
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	103 mm
Overall weight	0.178 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Straight
Swivel bearing	Stem, swiveling
Offset	27 mm
Swivel radius	73 mm
Swivel interference	146 mm

## FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

# LEVINA LIGHT

5225PJP075L51-10

EAN 4031582477061



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

