

STYLEA

5920UJI065S70-10X15

EAN 4031582456011



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.91 in
Overall width	1.65 in
Overall weight	0.39 lb

WHEEL

Body material	Polyamide
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	0.28 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	2.44 in
Swivel interference	4.17 in
Dome diameter	0.87 in
Thread diameter	0.39 in

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	0.59 in