

NOVATECH

ITB125X50-Ø17 H7

EAN 4031582397888
Order number 00861396



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Bore with keyway
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Axle hole diameter	17 mm
Hub length	54 mm
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	500 kg
Load capacity at 6 km/h	400 kg
Load capacity Static	1000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.795 kg

NOVATECH

ITB125X50-Ø17 H7

EAN 4031582397888
Order number 00861396



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

