

PRODUCT INFORMATION

# NOVATECH

RK.ETP075x50-Ø47x12

EAN 4031582369496



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

Body material	Undefined
Tread Material Mix	Polypropylene, soft
Diameter	75 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A
Ball bearing diameter	47 mm
Ball bearing width	12 mm

### PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

### CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	500 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.55 kg

# NOVATECH

RK.ETP075x50-Ø47x12

EAN 4031582369496



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

