

PRODUCT INFORMATION

NOVATECH

FTP 250x80-Ø25 HL92

EAN 4031582319415



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES


Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	4761.98 lb
Load capacity at 3.7 mph	3968.32 lb
Electric conductive	no
Stainless	no
Load capacity Static	7936.63 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	20.33 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	9.84 in
Tread width	3.15 in
Axle hole diameter	0.98 in
Hub length	3.62 in
Body width	3.15 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D




PRODUCT INFORMATION

NOVATECH

FTP 250x80-025 H192

EAN 4031582319415

Order number 10800997



BETTER MOBILITY. BETTER LIFE.