PRODUCT INFORMATION

ELASTECH

IFP 160x50-Ø20 HL60

Order number 00805136

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Aluminum
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Wheel color	Gray / non- marking
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll Performance	●●○○○
Movement noise	●●●●●
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	771.62 lb
Load capacity at 3.7 mph	617.29 lb
Electric conductive	no
Stainless	no
Load capacity Static	1543.23 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	2.65 lb

© Copyright 2026 TENTE International GmbH


ELASTECH

IFP 160x50-Ø20 HL60

Order number 00805136

BETTER MOBILITY. BETTER LIFE.

Product Drawings




© Copyright 2026 TENTE International GmbH

ELASTECH

IFP 160x50-Ø20 HL60

Order number 00805136



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH