

ELASTECH

IEP 300x55-Ø20 HL66

EAN 4031582319781



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOČAK

Tread hardness	mekan
Materijal za telo	Aluminijum
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglicni lezaj
Boja Tocak	Crni mlaz (sličan RAL9005)
stitnici omotaca	Bez stražara
Prečnik	300 mm
Širina omotac	55 mm
dimenzija rupa osovina	20 mm
dužina glavčine	66 mm
Širina tela	55 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	600 kg
Nosivost na 6 km/h	480 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	3.89 kg

ELASTECH


IEP 300x55-Ø20 HL66

EAN 4031582319781

Broj porudžbine 00834703
Product Drawings



BETTER MOBILITY. BETTER LIFE.




ELASTECH

IEP 300x55-Ø20 H66

EAN 4031582319781

Broj porudžbine 00804703



BETTER MOBILITY. BETTER LIFE.