

STEM

S70-10X15 / 10 DRILLED STEM

EAN 4031582411904



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Overall height	6 mm
Overall weight	0.025 kg

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	15 mm