

NOVATECH

FTP250X80-Ø35 HL90 TFR

EAN 4031582389548



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	9.84 in
Tread width	3.15 in
Axle hole diameter	1.38 in
Hub length	3.54 in
Hardness of tread (A)	92 Shore A

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	4761.98 lb
Load capacity at 3.7 mph	3968.32 lb
Load capacity Static	9523.96 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	26.25 lb

TECHNICAL DRAWINGS

