

# PURETECH

PVR 250x60-Ø25

EAN 4031582321340



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ○ ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ● ○ ○
otpornost na rdju	● ● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	295 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	590 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	2.87 kg

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
Boja Tocak	Grafitna crna (RAL9011)
štيتnici omotaca	Bez stražara
Prečnik	250 mm
Širina omotac	60 mm
dimenzija rupa osovina	25 mm
dužina glavnice	74 mm
Širina tela	60 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

# PURETECH

PVR 250x60-Ø25

EAN 4031582321340

Broj porudžbine 00050608  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

