

NOVATECH

ETY 080x25-Ø25

EAN 4031582369427



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity at 6 km/h	130 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.38 kg

WHEEL

Body material	Steel, iron
Tread Material Mix	PUR casted premium
Bearing	Precision ball bearing (RS/2RS)
Wheel Color	Honey yellow (RAL1005)
Diameter	80 mm
Tread width	25 mm
Axle Hole Diameter	25 mm
Hub Length	12 mm
Body width	25 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

