

NOVATECH

ITP 125X50-Ø25 HL60 CV

EAN 4031582330489
Order number 00839128



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread profile	convex
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Axle hole diameter	25 mm
Hub length	60 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	500 kg
Load capacity at 6 km/h	400 kg
Load capacity Static	1000 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.757 kg

NOVATECH

ITP 125X50-Ø25 HL60 CV

EAN 4031582330489
Order number 00839128



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

