

NOVATECH

RK.ETP075X50-Ø47X12

EAN 4031582369496



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	75 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A
Ball bearing diameter	47 mm
Ball bearing width	12 mm

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 3 km/h	500 kg
Load capacity Static	1000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.549 kg

TECHNICAL DRAWINGS

