

# PURETECH

PIP150X32-Ø8

EAN 4031582356694  
Broj porudžbine 00038560

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	polipropilen
	mekan
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	32 mm
dimenzija rupa osovina	8 mm
dužina glavcine	36,5 mm
Teškoća gazećeg omotac (A)	75 Šor A

## PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,43 kg

# PURETECH

PIP150X32-Ø8

EAN 4031582356694  
Broj porudžbine 00038560



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

