

MAXTECH

UAR100X36H45

EAN 4031582426953



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Bolt diameter	8 mm
Bolt length	65 mm

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Load capacity at 3 km/h	200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	-4080 °C
Overall weight	0.329 kg

WHEEL

Diameter	100 mm
Tread width	36 mm
Axle hole diameter	12 mm
Hub length	45 mm
Bearing type	Roller Bea