

NOVATECH

ETP 085X95-Ø20 HL95

EAN 4031582318821
Order number 00801060



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	3.35 in
Tread width	3.74 in
Axle hole diameter	0.79 in
Hub length	3.74 in
Body width	3.74 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Bearing type	6204

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1984.16 lb
Load capacity at 3.7 mph	1587.33 lb
Load capacity Static	3968.32 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	3.38 lb

TECHNICAL DRAWINGS

