

MAXTECH

PA0075X25-Ø8

EAN 4031582454291



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 3 km/h	60 kg
Load capacity Static	120 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.075 kg

WHEEL

Diameter	75 mm
Tread width	25 mm
Axle hole diameter	8.1 mm
Hub length	26.5 mm
Hardness of tread (D)	42 Shore D