

## NOVATECH

ITP150x50-Ø20-SH80A convex

EAN 4031582329513



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK


|                            |                          |
|----------------------------|--------------------------|
| Tread profile              | konveksan                |
| Materijal za telo          | Aluminijum               |
| materijal omotaca          | Poliuretana, liveno      |
| Nošenje                    | precizini kuglicni lezaj |
| stitnici omotaca           | Bez stražara             |
| Prečnik                    | 150 mm                   |
| Širina omotac              | 50 mm                    |
| dimenzija rupa osovina     | 20 mm                    |
| dužina glavnice            | 60 mm                    |
| Teškoća gazećeg omotac (A) | 80 Šešelj A              |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ○ ○ |
| Buka u pokretu         | ● ● ● ○ ○ |
| Ishrana                | ● ● ● ● ○ |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI


|                                |                              |
|--------------------------------|------------------------------|
| Naziv proizvoda                | Novatech                     |
| Tip                            | Tocak                        |
| Standard                       | EN12532 - transportna oprema |
| Nosivost na 4 km/h             | 500 kg                       |
| Nosivost na 6 km/h             | 400 kg                       |
| Električni provod              | no                           |
| nerdjajući                     | no                           |
| Statički Nosivost              | 1000 kg                      |
| Temperaturni opseg (Minimalno) | -10 °C                       |
| Opseg temperature (maksimalni) | 60 °C                        |



**NOVATECH**

ITP150x50-Ø20-SH80A convex

EAN 4031582329513



BETTER MOBILITY. BETTER LIFE.