PRODUCT INFORMATION

ALPHA

3478UAR125P63 CL60 OH161 WB-natural

EAN 4031582306859



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Alpha
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Electric Conductive	No
Stainless	No
Load capacity Static	600 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall Height	161 mm
Overall width	115 mm
Overall weight	1.39 kg

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Housing Color	Blue passivated

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Roller bearing
Axle	Screwed with nut
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Body width	40 mm
Hardness of tread (A)	96 Shore A
Hardness of tread (D)	50 Shore D

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	115 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

© Copyright 2026 TENTE International GmbH


ALPHA


3478UAR125P63 CL60 OH161 WB-natural

EAN 4031582306859

Order number 00028790

Product Drawings





© Copyright 2026 TENTE International GmbH