

AGILA CARE

2476PJP100R26-28S45 D

EAN 4031582301793
Order number 00006453



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila care
Type	Swivel castor with central , total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	5.43 in
Overall width	2.36 in
Overall weight	1.8 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.26 in
Body width	1.26 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Color	Blue passivated
Offset	1.5 in
Swivel radius	3.46 in
Swivel interference	6.93 in
Dome diameter	2.36 in

FITTING

Fitting type	Stem with cam hole for profile bars
Bolt diameter	1.1 in
Bolt length	3.78 in
Bolt thread position	0.75 in
Bolt mounting holes quantity	2

AGILA CARE

2476PJP100R26-28S45 D

EAN 4031582301793
Order number 00006453



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

