PRODUCT INFORMATION

# LINEA LIGHT

5925XSO075L51-10 RAL7001

EAN 4031582399127

BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ● ● ○ ○ ○ |
| Movement Noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Linea light |
| Type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 90 kg |
| Electric Conductive | Yes |
| Stainless | No |
| Load capacity Static | 180 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 75.5 mm |
| Overall width | 55 mm |
| Overall weight | 0.15 kg |

## HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel Bearing | Stem, swiveling |
| Housing Color | Silver grey (RAL7001) |
| Offset | 23 mm |
| Swivel radius | 81 mm |
| Swivel interference | 162 mm |
| Dome diameter | 30 mm |

## WHEEL

| | |
|---|---|
| Body material | Polyamide, electric conductive |
| Tread Material Mix | Polyurethane, injected, electric-conductive |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 75 mm |
| Tread width | 15 mm |
| Hardness of tread (A) | 92 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 10 mm |

Deutscher Designer Club

Interzum Award

IF Design Award

© Copyright 2026 TENTE International GmbH


# LINEA LIGHT


5925XSO075L51-10 RAL7001

EAN 4031582399127

Order number 00770565

**Product Drawings**





© Copyright 2026 TENTE International GmbH