PRODUCT INFORMATION

# DURATECH

## UOP125x46-Ø20 HL60

EAN 4031582442823

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread Material Mix | Identical with wheel body |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 125 mm |
| Tread width | 46 mm |
| Axle Hole Diameter | 20 mm |
| Hub Length | 60 mm |
| Hardness of tread (D) | 75 Shore D |

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●● |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●● |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Duratech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 300 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 600 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.51 kg |

© Copyright 2026 TENTE International GmbH


# DURATECH

## UOP125x46-Ø20 HL60

EAN 4031582442823

BETTER MOBILITY. BETTER LIFE.

### Product Drawings




© Copyright 2026 TENTE International GmbH