

PRODUCT INFORMATION

DURATECH

UOR080x34-Ø12 HL44,4

EAN 4031582442755



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	80 mm
Tread width	34 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	180 kg
Electric Conductive	No
Stainless	No
Load capacity Static	360 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.12 kg

DURATECH

UOR080x34-Ø12 HL44,4

EAN 4031582442755



BETTER MOBILITY. BETTER LIFE.

Product Drawings

