

ALPHA

3477UER160P30-13

EAN 4031582305838



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	195 mm
Overall weight	2.337 kg

WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	46 mm
Hardness of tread (A)	64 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	60 mm
Swivel radius	167 mm
Swivel interference	334 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

ALPHA

3477UER160P30-13

EAN 4031582305838



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

