

LINEA LIGHT

5925PJI050L51-10 RAL9002

EAN 4031582439311



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Linea light
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	50.5 mm
Overall width	47.6 mm
Overall weight	0.072 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Tread width	13 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	15 mm
Swivel radius	52 mm
Swivel interference	104 mm
Dome diameter	23 mm

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm

Deutscher
Designer
ClubInterzum
AwardIF
Design
Award

LINEA LIGHT

5925PJI050L51-10 RAL9002

EAN 4031582439311



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

