


NOVATECH

ETY 080X20-Ø20 EL14

EAN 4031582318524
Broj porudžbine 00830219

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj (RS/2RS)
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	80 mm
Širina omotac	20 mm
dimenzija rupa osovina	20 mm
dužina glavčine	14 mm
Širina tela	20 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	140 kg
Nosivost na 6 km/h	110 kg
Statički Nosivost	280 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,3 kg

NOVATECH

ETY 080X20-Ø20 EL14

EAN 4031582318524
Broj porudžbine 00830219



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

