

DURATECH

UOP125x40-Ø8 HL45

EAN 4031582442816



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.31 in
Hub length	1.77 in
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Electric conductive	no
Stainless	no
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	0.76 lb

DURATECH

UOP125x40-Ø8 HL45

EAN 4031582442816



BETTER MOBILITY. BETTER LIFE.

Product Drawings

