

ALPHA STAINLESS

8477PIO100P62

EAN 4031582381658
Broj porudžbine 00038381

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha stainless
Tip	Okreni Tocak sa potpuna kocnica
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	75 kg
nerdjajuci	✓
Statički Nosivost	150 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	128 mm
Ukupna težina	0,998 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	klizni lezaj
osovina	Završena sa navrtkom
stirnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	35 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

KUCISTE

Materijal	nerdjajuci čelik, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	41 mm
okretni radijus	123 mm
Otpor okretanju	246 mm

PRILAGODAVANJE

Tip uklapanja	Pravougaona ploča
Dužina ploče	105 mm
Širina ploče	80 mm
Dužina otvora ploče (Minimalno)	77 mm
Dužina otvora ploče (maksimalna)	80 mm
Širina otvora ploče (maksimalna)	60 mm
Prečnik otvora ploče	9 mm

ALPHA STAINLESS

8477PIO100P62

EAN 4031582381658
Broj porudžbine 00038381



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

3477U00100P62-neu

