

# LUMINA

AA20PJ1050P41-38X38 TFR

EAN 4031582385632



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product name                | Lumina                      |
| Type                        | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 3 km/h     | 40 kg                       |
| Load capacity Static        | 80 kg                       |
| Temperature range (Minimum) | -10 °C                      |
| Temperature range (Maximum) | 40 °C                       |
| Overall height              | 63 mm                       |
| Overall width               | 55 mm                       |
| Overall weight              | 0.105 kg                    |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread material        | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Threadguards          | Without threadguard            |
| Diameter              | 50 mm                          |
| Tread width           | 10 mm                          |
| Hardness of tread (A) | 87 Shore A                     |

## HOUSING

|                     |                            |
|---------------------|----------------------------|
| Material fork       | Polypropylene              |
| Fork shape          | Twin wheel housing, closed |
| Swivel bearing      | Stem, swiveling            |
| Swivel radius       | 49 mm                      |
| Swivel interference | 98 mm                      |

## FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 38 mm        |
| Plate width                 | 38 mm        |
| Plate hole length (Maximum) | 28 mm        |
| Plate hole width (Maximum)  | 28 mm        |
| Plate hole diameter         | 4.4 mm       |