

# AGILA

R07-Ø21,5-24 INOX\_TBE

EAN 4031582437829



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Corrosion resistance ● ● ● ○ ○

## CORE ATTRIBUTES

|                             |           |
|-----------------------------|-----------|
| Product name                | Agila     |
| Housing type                | Accessory |
| Temperature range (Minimum) | -10 °C    |
| Temperature range (Maximum) | 40 °C     |
| Overall weight              | 0.126 kg  |

## HOUSING

|           |   |
|-----------|---|
| Stainless | ✓ |
|-----------|---|

## FITTING

|                            |  |
|----------------------------|--|
| Fitting type               | Synthetic expander, round                                  |
| Expander fitting (Minimum) | 21.5 mm  |
| Expander fitting (Maximum) | 24 mm  |
| Hint                       | Please indicate required tube innerdiameter when ordering. |